# **Ninox SWIR 640**

High resolution, low noise, cooled, digital VIS-SWIR camera  $640 \times 512 \cdot \text{Cooled}$  to  $-20^{\circ}\text{C} \cdot < 50e$  in high gain  $\cdot$ 





# **Key Features and Benefits**

The best performing SWIR camera in the World!

- Cooled VIS-SWIR technology
   Cooled to -20°C. Enables low dark current and longer exposure
- 15μm x 15μm pixel pitch
  Enables highest resolution VIS-SWIR image
- <50e in high gain</li>
   Enables highest VIS-SWIR detection limit
- Ultra high intrascene dynamic range 70dB

  Enables similtaneous capture of bright & dark portions of a scene
- On-board intelligent 3 point NUC Enables highest quality images

Resolution	640 x 512
Frame Rate	Up to 120Hz
Cameralink	14 bit
Wavelength Range VIS-SWIR	
Dark Current	<1,500 e/p/s



## **Specification for Ninox SWIR 640**

Sensor	SCD
Sensor Type	InGaAs PIN-Photodiode
Active Pixel	640 x 512
Pixel Pitch	15µm x 15µm
Active Area	9.6mm x 7.68mm
Spectral response <sup>1</sup>	0.4μm to 1.7μm
Noise (RMS)	<195 electrons Low Gain, <50 electrons High Gain
Quantum Efficiency	Peak >85% (>73% @ 1.064μm, 78% @ 1.55μm)
Pixel Well Depth	650Ke Low Gain, 12Ke High Gain
Pixel Operability	>99.5%
Dark Current	<1,500e/p/s @-20°C
Digital Output Format	14 bit CameraLink (Base Configuration)
Exposure time	10µs to 26.8sec or 1/frame rate Low Gain 100µs to 26.8sec or 1/frame rate High Gain
Shutter mode	Global shutter
Frame Rate	up to 120Hz
Optical Interface	C-mount (selection of SWIR lens available)
Camera Setup / Control	CameraLink
Dynamic Range	14 bit
Trigger interface	Trigger IN and OUT - TTL compatible
Power supply	12V DC ±10%
TE Cooling	to -35°C Delta
Image Correction	
. 3	3 point NUC (offset, Gain & Dark Current) + pixel correction
Functions controlled by serial communication	3 point NUC (offset, Gain & Dark Current) + pixel correction  Exposure, intelligent AGC, Non Uniformity Correction, Gamma, Pk/ Av, TEC, ROI
Functions controlled by serial	Exposure, intelligent AGC, Non Uniformity Correction, Gamma, Pk/
Functions controlled by serial communication	Exposure, intelligent AGC, Non Uniformity Correction, Gamma, Pk/Av, TEC, ROI
Functions controlled by serial communication  Camera Power Consumption <sup>2</sup>	Exposure, intelligent AGC, Non Uniformity Correction, Gamma, Pk/Av, TEC, ROI  < 4W with TEC OFF (Typical)

**Ordering Information** 

#### Camera

NINOX 640 VIS-SWIR digital NX1.7-VS-CL-640 camera

NINOX Power Supply Cable RPL-HR4-K

 $\begin{array}{lll} \text{Chiller} & \text{RPL-AMS-OASIS160}^4 \\ \text{Chiller Tubing} & \text{RPL-WTUBE-NINOX}^5 \\ \text{Water cooling system} & \text{RPL-WCUK-WCS} \\ \end{array}$ 

#### **Optional Accessories**

EPIX(R) base CL card RPL-EPIX-EB1

EPIX(R) base notebook CL card RPL-EPIX-ECB1-34

EPIX(R) base notebook CL card RPL-EPIX-ECB1-54

EPIX(R) XCAP STD sofware RPL-XCAP-STD

CameraLink Cable, 2m<sup>6</sup> RPL-CL-CBL-2M

Optical SWIR lenses<sup>7</sup> RPL-xx-xxxx

Note 1: Optional filters available: Low, High or bandpass

Note 2: Measured @ 30°C

Note 3: Extended Operating Temperature range on request

Note 4: This includes the chiller and the liquid Note 5: This includes the tube + connectors


Note 6: Longer CL cable available

Note 7: Please consult us to check our range of lenses

Demo is available on request. Pricing AOR subject to volumes.

Detailed technical drawings can be downloaded at www.raptorphotonics.com

## **Quantum Efficiency**



Raptor Photonics Limited reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

# **Applications**

- Astronomy
- Beam Profiling
- Hyperspectral Imaging
- Semiconductor Inspection
- Solar Cell Inspection
- Thermography
- Microscopy
- Art Inspection

Document #: INNINOX 1.7-VS-CL-640 0116R1

