


Eagle XO

Open Front, Direct detection CCD

2048 x 2048 and 2048 x 512 formats • 75kHz and 2MHz • High resolution soft X-ray scientific imaging



Key Features and Benefits

Ultimate Sensitivity Performance

- **Open front end**
CF152 (6") flange for direct interfacing to vacuum chambers
- **Deep cooled using Thermoelectric cooler (TEC)**
Minimize dark current and enable long exposure
- **Back Illuminated with no coating**
Optimizes sensitivity and large field of view imaging
- **13.5 μ m x 13.5 μ m pixels**
Enables ultra sharp image resolution and high dynamic range

Resolution	2048 x 2048 2048 x 512
------------	---

Dark Current	0.0004 e/p/s
--------------	---------------------

Readout Noise	2.3 e/p RMS
---------------	--------------------

Cameralink	16bit
------------	--------------

Specification for Eagle XO

Sensor	E2V 4240 Back Illuminated, AIMO ¹	E2V 4210 Back Illuminated, AIMO ¹
Active Pixel Array Size	2048 × 2048 pixels	2048 × 512 pixels
Pixel Size	13.5µm × 13.5µm	
Active Area	27.65mm × 6.9mm (28.45mm diagonal)	27.65mm × 27.65mm (39.10mm diagonal)
Binning	Programmable, up to 64×64 pixels	
Full Well Capacity	100,000 e/p	
Non-Linearity	< 1%	
Readout Noise	@ 75kHz pixel readout rate, 2.3 e/p @ 2MHz pixel readout rate, 9.0 e- rms	
Binned Read Noise	@75kHz pixel readout rate, 16×16 binning < 5.0 e- rms	
Peak Quantum Efficiency (QE)	> 90%	
Spectral Response	1.2eV to 20KeV	
Dark Current @ -75°C (typical)	0.0004 e-/pixel/second	
Cooling Active	ΔT > 100°C, -75°C air cooled / -80°C water cooler	
Cooling Method	Air / Liquid	
Flange	CF152 (6") 2	
Synchronization	Trigger IN and OUT – TTL compatible	
Digital Output	16-bit	
Data Interface	CameraLink (base)	
Power Supply	12V DC ±10%	
Total Power Consumption	TEC OFF < 9W TEC ON < 100W	
Operating Temperature Range	-20°C to +55°C	
Storage Temperature Range	-40°C to +70°C	
Dimensions	141mm x 133mm x 110mm	
Weight (excluding lens)	5.0kg [11lb]	

Raptor Photonics Limited reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

Ordering Information

Camera

Eagle XO Open Front CCD 4MP	EA4240XO-BN-CL
Eagle XO Open Front CCD 1MP	EA4210XO-BN-CL
Eagle XV Power Supply unit	E4240XV-PSU

Optional Accessories

EPIX(R) EB1 base CL card	RPL-EPIX-EB1
EPIX(R) base notebook CL card	RPL-EPIX-ECB1-34
EPIX(R) base notebook CL card	RPL-EPIX-ECB1-54
EPIX(R) XCAP STD software	RPL-XCAP-STD
CameraLink Cable, 2m ³	RPL-CL-CBL-2M
Water cooler (Recommended coolant flow rate >0.5liters per min. & cooling capacity >100W @ 20°C)	Contact us for order information

Note 1: Other sensors options available on request

Note 2: Other flange options available such as ISO-K-DN100-

Note 3: Longer CL cable available


Note 4: Please consult us to check our range of lenses

Note 5: A range of coatings are available

Demo is available on request.
Pricing AOR subject to volumes.

Detailed technical drawings
can be downloaded at
www.raptorphotronics.com

Quantum Efficiency



Applications

Document #: INEA4240XV-CL 0217R1